


Foot mounting DAMH-Q12-40

Part number: 3371846

FESTO



Data sheet

Feature	Value
Size	40
Assembly position	Any
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	0 ... 60 °C
Max. tightening torque	18 Nm
Product weight	529 g
Mounting type	with through hole
Materials note	Conforms to RoHS
Material bracket	steel, galvanized