


Exhaust flow control valve GRE-3/8

Part number: 35310

FESTO

With sintered metal silencer.



Data sheet

| Feature | Value |
|--|---|
| Valve function | Flow control – silencer function |
| Pneumatic connection, port 1 | G3/8 |
| Adjusting element | Slotted head screw |
| Mounting type | Threaded |
| Standard nominal flow rate in flow control direction | 2,000 l/min |
| Standard flow rate 0.6->0 MPa (6->0 bar, 87->0 psi) | 3 ... 2,000 l/min |
| Working pressure | 0 ... 10 bar |
| Ambient temperature | -10 ... 70 °C |
| Assembly position | Any |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| PWIS conformity | VDMA24364-B1/B2-L |
| Medium temperature | -10 ... 70 °C |
| Max. tightening torque | 15 Nm |
| Product weight | 50 g |
| Material of threaded plug | Wrought Aluminum alloy |
| Materials note | Conforms to RoHS |
| Material seals | NBR |
| Material adjusting screw | Brass |