


# Silencer U-PK-3

Part number: 4646

FESTO

For reducing noise and avoiding contamination at the exhaust ports of pneumatic components.



## Data sheet

Feature	Value
Assembly position	Any
Operating pressure MPa	0 ... 1 MPa
Working pressure	0 ... 10 bar
Flow rate to atmosphere	310 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
PWIS conformity	VDMA24364-B1/B2-L
Sound pressure level	70 dB(A)
Ambient temperature	-10 ... 70 °C
Product weight	4.5 g
Pneumatic connection	PK-3
Material of silencer insert	Bronze
Material of threaded plug	Brass
Materials note	Conforms to RoHS