


Coupling

EAMD-67-51-16-32X32-U

Part number: 5071095

FESTO



Data sheet

Feature	Value
Holder diameter 1	16 mm
Holder diameter 2	32 mm
Size	67
Nominal length	51 mm
Assembly position	Any
Max. speed	4,500 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 ... 60 °C
Mass moment of inertia	374 kgmm ²
Transferable torque	93 Nm
Product weight	750 g
Materials note	Conforms to RoHS