


Manifold block MHA3-PR6-3-1/8

Part number: 525223

FESTO

for manifold block valves MHA3-....-HC/TC



Data sheet

Feature	Value
Max. number of valve positions	6
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Mounting method for subbase	with through hole with top-hat rail
Mounting method for valve	with internal (female) thread
Pneumatic ports 1/33	G1/4
Pneumatic connection, port 2	Female thread G1/8
Pneumatic ports 3/11	G1/4
Material of connecting plate	Wrought Aluminum alloy