

Pressure regulator LR-QS4-D-O-7-MICRO

Part number: 526270



Classic - do not use for new projects

Subbase with push-in connector, without pressure gauge

Modern alternatives can be found by entering the first four characters of the type code in the search field.

Type to be discontinued. Available until 2023. See Support Portal for alternative products.

FESTO



Data sheet

Feature	Value
Size	Micro
Series	D
Actuator lock	Rotary knob with lock
Assembly position	Any
Design structure	directly-controlled diaphragm regulator
Controller function	with secondary exhaust
Pressure gauge	M5 ready
Working pressure	1 ... 10 bar
Pressure regulation range	0.5 ... 7 bar
Max. pressure hysteresis	0.3 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4] Inert gases
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [7:4:4] Inert gases
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Product weight	100 g
Mounting type	Line installation with accessories Optional
Pneumatic connection, port 1	QS-4
Pneumatic connection, port 2	QS-4
Materials note	Conforms to RoHS
Material of connecting plate	Wrought Aluminum alloy
Material seals	NBR
Material housing	Wrought Aluminum alloy
Material membrane	NBR