


Linear actuator DGC-8- -

Part number: 530906

★ Core product range

Other stroke lengths upon request. Refer to the catalog pages (PDF) for the characteristic load values.

FESTO



Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Stroke	1 ... 2,000 mm
Piston diameter	8 mm
Cushioning	P: Flexible cushioning rings/plates at both ends YSR: Shock absorber, hard characteristic curve YSRW: Shock absorber, soft characteristic curve
Assembly position	Any
Guide	Basic guide Recirculating ball bearing guide
Position detection	For proximity sensor
Variants	Additional slide, on left as standard Additional slide, on right as standard
Operating pressure MPa	0.25 ... 0.8 MPa
Working pressure	2.5 ... 8 bar
Mode of operation	double-acting
CE symbol (see declaration of conformity)	according to EU-Ex protection guideline (ATEX)
UKCA marking (see declaration of conformity)	To UK EX instructions
Explosion protection certification outside the EU	EPL Dc (GB) EPL Gb (GB)
ATEX category Gas	II 2G
ATEX category Dust	II 3D
Explosion ignition protection type Gas	Ex h IIC T4 Gb X
Explosion ignition protection type Dust	Ex h IIIC T120°C Dc X
Explosion-proof ambient temperature	+5°C ≤ Ta ≤ +60°C
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress 2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	30 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	30 N
Mounting type	with accessories
Materials note	Conforms to RoHS
Material cover	Wrought Aluminum alloy
Material seals	POM TPE-U(PU)