

Plug FBS-SUB-9-BU-2X5POL-B

Part number: 532219

FESTO

For DeviceNet, CANopen



Data sheet

| Feature | Value |
|-----------------------------------|--|
| Width | 20 mm |
| Height | 62 mm |
| Length | 61 mm |
| Protocol | CAN |
| Product weight | 60 g |
| Fieldbus interface | 2x 5 spring-loaded terminals |
| Note regarding fieldbus interface | Bus in – bus out looped through |
| Permissible cable diameter | 5 ... 10 mm |
| Protection class | IP65 IP67 in assembled condition to IEC 60529 |
| Ambient temperature | 0 ... 50 °C |
| Storage temperature | -20 ... 70 °C |
| Relative air humidity | 95 % non-condensing |
| PWIS conformity | VDMA24364-B2-L |
| Materials note | Conforms to RoHS |
| Material housing | PA-reinforced |
| Material of union nut | Brass |
| Material screws | Steel |
| Material seals | NBR |