

Sub-base-SET MS12-AGI

Part number: 537138

FESTO

From the MS series, with G thread.



Data sheet

Feature	Value
Size	12
Series	MS
Assembly position	Any
Operating medium	Air quality class 5:7:- per DIN ISO 8573-1
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-10 ... 60 °C
Medium temperature	-10 ... 60 °C
Product weight	1,300 g
Pneumatic connection, port 1	G2
Pneumatic connection, port 2	G2
Materials note	Conforms to RoHS
Material of connecting plate	Aluminum die cast
Material seals	NBR