



Vertical pressure supply plate

VABF-S2-1-P1A3-N38

Part number: 546094

FESTO

For valve manifold VTSA, standard port pattern to 5599-1, 5599-2, for mounting between manifold sub-base and valve.



Data sheet

Feature	Value
Width	43 mm
Based on the standard	ISO 5599-2
Assembly position	Any
Pneumatic vertical stacking	Alternative pressure supply for 1
Operating pressure MPa	-0.09 ... 1 MPa
Working pressure	-0.9 ... 10 bar
Standard nominal flow rate	1,300 l/min
CE symbol (see declaration of conformity)	According to EU simplified Pressure Vessel Directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Protection class	IP65 NEMA 4
Ambient temperature	-5 ... 50 °C
Product weight	340 g
Vertical stacking type of mounting	on manifold block on individual subbase
Materials note	Conforms to RoHS
Material housing	Aluminum die cast