



Basic valve LOE-D-MAXI-U

Part number: 546517
Classic - do not use for new projects



Without threaded connection plates with FRB threaded pin, with metal bowl guard.

Modern alternatives can be found by entering the first four characters of the type code in the search field.



Data sheet

Feature	Value
Size	Maxi
Series	D
Assembly position	Vertical +/- 5°
Design structure	proportional standard mist lubricator
Max. oil capacity	6.46 oz(l)
Bowl guard	Metal bowl guard
Working pressure	0 ... 240 Psi
Minimum flow rate for lubricator function	0.35 cfm
Standard nominal flow rate	294 cfm
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	14 ... 140 °F
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [7:4:-] Inert gases
Medium temperature	14 ... 140 °F
Ambient temperature	14 ... 140 °F
Product weight	42 oz
Mounting type	with accessories
Materials note	Conforms to RoHS
Material bowl	PC