

Plastic tubing PUN-5/16X1/16-U-WS

Part number: 546597

FESTO

standard O.D. tubing, suitable for QS and QB push-in fittings.

This product is only available if ordered from the Festo Corporation, USA.

Old part no. 13016603



Data sheet

Feature	Value
Outer diameter, inches	5/16
Inner diameter, inches	3/16
Min. bending radius	0.594 "
Temperature dependent working pressure	-14 ... 150 Psi
Operating medium	Filtered compressed air Vacuum
Ambient temperature	-68 ... 140 °F
Product weight according to length	0.412 oz/ft
Color	white
Shore hardness	A 98 +/-3
Materials note	Free of copper and PTFE
Materials information for tubing	TPE-U(PU)