


Regulator plate VABF-S3

Part number: 546837

FESTO

For valve manifold VDMA-01/02, standard port pattern to ISO 15407-1.



Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Based on the standard	ISO 15407-1
Assembly position	Any
Controller function	Output pressure constant with secondary exhaust
Pressure gauge selection	possible
Inlet pressure 1	0.5 ... 10 bar
Operating medium	Filtered compressed air, grade of filtration 40 µm, lubricated or unlubricated
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Protection class	IP65 NEMA 4
Ambient temperature	-5 ... 50 °C
Vertical stacking type of mounting	on manifold block on individual subbase
Pressure gauge connection	with retaining clamp
Materials note	Conforms to RoHS
Material control panel	PA
Material regulator housing	Aluminum die cast