

# Cable

## SBOA-K20CP-SUP

Part number: 548824

FESTO

For SBOI-Q-... and SBOC-Q-... compact vision systems



## Data sheet

Feature	Value
Mounting type	With sleeve nut
Assembly position	Any
Electrical connection	Straight plug / straight socket / straight socket
Operating voltage range DC	≤ 60 V
Cable length	2 m
Cable attribute	Suitable for chain link trunking
Cable diameter	5.5 mm
Cable structure	2x0,24+2x0,34+0,49
Protection class	IP65 IP67 to IEC 60529
Ambient temperature	-20 ... 80 °C
Ambient temperature with flexible cable installation	-5 ... 80 °C
Materials note	Conforms to RoHS
Corrosion resistance classification CRC	1 - Low corrosion stress
Material cable sheath	PUR
Cable sheath color	light grey
Material housing	Aluminum die cast Brass PUR Nickel plated
Material electrical contact	bronze / brass Gold plated