


Connector block CPE18-PRS-3/8-6-NPT

Part number: 550092
Classic - do not use for new projects

FESTO

For CPE valves.

Modern alternatives can be found by entering the first four characters of the type code in the search field.



Data sheet

| Feature | Value |
|---|-------------------------------|
| Grid dimension | 26 mm |
| Assembly position | Any |
| Max. number of valve positions | 6 |
| Max. no. of pressure zones | 2 |
| Burst pressure | 5 MPa |
| Bursting pressure | 50 bar |
| Burst pressure | 725 psi |
| Operating pressure MPa | -0.09 ... 1 MPa |
| Working pressure | -0.9 ... 10 bar |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Medium temperature | 23 ... 122 °F |
| Ambient temperature | 23 ... 122 °F |
| Max. tightening torque, valve mounting | 1.5 ft-lbf |
| Product weight | 30.45 oz |
| Type of mounting in-line valve manifold | with through hole |
| Mounting method for valve | with internal (female) thread |
| Pneumatic connection, port 1 | 3/8 NPT |
| Pneumatic connection, port 3 | 3/8 NPT |
| Pneumatic connection, port 5 | 3/8 NPT |
| Materials note | Conforms to RoHS |
| Material manifold | Wrought Aluminum alloy |