

Fibre-optic cable SOOC-TB-M4-2-R25

Part number: 552812

FESTO

Suitable for SOE4 fiber-optic units.



Data sheet

Feature	Value
Materials note	Conforms to RoHS
Measurement method	Through-beam sensor
Minimal object diameter	0.35 mm
Fiber-optic cable - special feature	Standard
Working range	400 mm
Ambient temperature	-55 ... 70 °C
Size, head	M4
Fiber optic cable length	2 m
Min. bending radius	25 mm
Max. tightening torque	2 Nm
Outside diameter	2.2 mm
Material housing	Copper alloy PVC Nickel plated
Material fibre-optic	PE
Protection class	IP66
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364 zone III