


Fibre-optic cable SOOC-DS-F-M4-2-R2

Part number: 552843

FESTO

Suitable for SOE4 fiber-optic units.



Data sheet

Feature	Value
Materials note	Conforms to RoHS
Measurement method	Diffuse reflection sensor
Minimal object diameter	0.1 mm
Fiber-optic cable - special feature	Flexible
Working range	130 mm
Ambient temperature	-40 ... 70 °C
Size, head	M4
Fiber optic cable length	2 m
Min. bending radius	2 mm
Max. tightening torque	2 Nm
Outside diameter	1.3 mm
Material housing	High alloy steel, non-corrosive
Material fibre-optic	PE
Protection class	IP66
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364 zone III