



Proximity Sensor SIEF-M18B-NS-S-L

Part number: 553547

FESTO

With plug, flush mounting



Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Authorization	RCM Mark c UL us - Listed (OL)
CE symbol (see declaration of conformity)	according to EU-EMV guideline
Materials note	Conforms to RoHS
Nominal switching distance	5 mm
Ambient temperature	-30 ... 85 °C
Repetition accuracy	0.28 mm
Switch output	NPN
Switching element function	Normally open contact
Max. switching frequency, DC	3,000 Hz
Max. output current	200 mA
Short circuit strength	Pulsing
Operating voltage range DC	10 ... 30 V
Polarity protected	for all electrical connections
Electrical connection	3-pin M12x1 Plug
Material connector housing	Brass Chromed-plated
Size	M18
Type of installation	flush
Product weight	41 g
Material housing	Brass Chromed-plated
Operating status display	Yellow LED
Protection class	IP68
Interference immunity to magnetic fields	DC and AC magnetic field
Surge strength	0.8 kV
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Degree of contamination	3