

Plug screw QSC-F-M5-I

Part number: 556855

FESTO

Metal design, temperature range up to 150°C.



Data sheet

Feature	Value
Size	Standard
Type of seal on screw-in stud	Sealing ring
Operating pressure complete temperature range	-0.95 ... 16 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	3
Food safety	to manufacturer's declaration
Ambient temperature	0 ... 150 °C
Authorization	Germanischer Lloyd
Max. tightening torque	1.5 Nm
Product weight	1 g
Materials note	Conforms to RoHS
Materials information, housing	Brass Chromium and nickel plated
Materials information for thread seal	FPM
Materials information for tubing seal	FPM