

Axial kit EAMM-A-E48-52C

Part number: 556995

FESTO

Suitable for electric drives.



Data sheet

Feature	Value
Assembly position	Any
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	17 Nm
Product weight	1,210 g
Interface code, actuator	E48A E48B
Interface code, motor in	52C
Materials note	Conforms to RoHS