


Axial kit EAMM-A-S62-100A

Part number: 558167

☆ Core product range

Suitable for electric drives.

FESTO



Data sheet

Feature	Value
Assembly position	Any
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	17 Nm
Product weight	2,050 g
Interface code, actuator	S62
Interface code, motor in	100A
Materials note	Conforms to RoHS