

# Coupling EAMC-56-58-19-25

Part number: 558315

FESTO



## Data sheet

Feature	Value
Holder diameter 1	19 mm
Holder diameter 2	25 mm
Size	56
Nominal length	58 mm
Assembly position	Any
Max. speed	5,500 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 ... 60 °C
Mass moment of inertia	128 kgmm <sup>2</sup>
Transferable torque	60 Nm
Product weight	275 g
Materials note	Conforms to RoHS