


# Axial kit

## EAMM-A-D32-35A-40A

Part number: 560281

FESTO

Suitable for electric drives.



## Data sheet

Feature	Value
Assembly position	Any
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	4 Nm
Product weight	220 g
Interface code, actuator	D32C
Interface code, motor in	35A
Materials note	Conforms to RoHS