


End plate VABE-S6-2RZ-G34

Part number: 560839

FESTO



Data sheet

Feature	Value
Based on the standard	ISO 5599-2
Assembly position	Any
Valve manifold type	44
Operating pressure MPa	-0.09 ... 1 MPa
Working pressure	-0.9 ... 10 bar
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Product weight	336 g
Pilot air port 12	G1/4
Pilot air port 14	G1/4
Pneumatic connection, port 1	G3/4
Pneumatic connection, port 3	G3/4
Pneumatic connection, port 5	G3/4
Materials note	Conforms to RoHS
Material end plate	Aluminum die cast