

Electrical link VMPAL-EVAP-20-1

Part number: 560965

FESTO



Data sheet

Feature	Value
Valve size	20 mm
Max. number of valve positions	1
Max. number of solenoid coils	1
Integrated function	Colour-coded assignment of the valve function
Nominal operating voltage DC	24 V
Corrosion resistance classification CRC	3 - High corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 ... 50 °C
Product weight	14 g
Housing color	Grey
Material housing	PA
Materials note	Conforms to RoHS