


Subbase

VMPAL-AP-20-QS8-1-T1

Part number: 561021

FESTO



Data sheet

Feature	Value
Width	21.2 mm
Length	107.3 mm
Grid dimension	21.2 mm
Valve size	20 mm
Pressure zone separation	Duct 1
Max. number of valve positions	1
Flow direction	reversible
Valve manifold structure	Valve sizes can be mixed
Max. number of solenoid coils	1
Operating pressure MPa	-0.09 ... 1 MPa
Working pressure	-0.9 ... 10 bar
Pilot pressure MPa	0.3 ... 0.8 MPa
Pilot pressure	3 ... 8 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	3 - High corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 ... 50 °C
Product weight	76.88 g
Pneumatic connection, port 2	For tubing outside diameter 8 mm
Pneumatic connection, port 4	for tubing, 8mm outside diameter
Materials note	Conforms to RoHS
Material of connecting plate	PA-reinforced