

Blanking plug QBC-3/16H-U

Part number: 564785

FESTO



Data sheet

| Feature | Value |
|---|---|
| Size | Standard |
| Assembly position | Any |
| Design | Blanking plug |
| Container size | 10 |
| Design structure | Push/pull principle |
| Operating pressure for entire temperature range | 0.095 ... 1 MPa |
| Operating pressure complete temperature range | 0.95 ... 10 bar |
| Operating pressure for entire temperature range | 13.775 ... 145 psi |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:::] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364 zone III |
| Ambient temperature | 0 ... 60 °C |
| Product weight | 0.035 oz |
| Pneumatic connection, port 1 | Push-in sleeve diameter 3/16" |
| Ambient temperature Fahrenheit | 32 ... 140 °F |
| Materials note | Conforms to RoHS |