


Blanking plug QBC-1/4H-U

Part number: 564786

FESTO



Data sheet

Feature	Value
Size	Standard
Assembly position	Any
Design	Blanking plug
Container size	10
Design structure	Push/pull principle
Operating pressure for entire temperature range	0.095 ... 1 MPa
Operating pressure complete temperature range	0.95 ... 10 bar
Operating pressure for entire temperature range	13.775 ... 145 psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:::]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364 zone III
Ambient temperature	0 ... 60 °C
Product weight	0.035 oz
Pneumatic connection, port 1	Push-in sleeve diameter 1/4"
Ambient temperature Fahrenheit	32 ... 140 °F
Materials note	Conforms to RoHS