

Plastic tubing

PEN-5/32-BL-150-CB

Part number: 569889

FESTO

standard O.D tubing, for QS plug connectors, polyethylene (not approved for use in the food industry).

This product is only available if ordered from the Festo Corporation, USA.



Data sheet

Feature	Value
Outer diameter, inches	5/32
Bending radius relevant for flow rate	0.065 Fuß
Min. bending radius	0.032 Fuß
Temperature dependent working pressure	-14.4 ... 145 Psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Ambient temperature	-22 ... 140 °F
Product weight according to length	0.067 oz/ft
Color	blue
Shore hardness	D 52 +/-3
Materials note	Conforms to RoHS Free of copper and PTFE
Materials information for tubing	PE