

# Plastic tubing PLN-5/8-NT-150-CB

Part number: 569903

FESTO

highly resistant to chemicals and hydrolysis.



## Data sheet

Feature	Value
Outer diameter, inches	5/8
Bending radius relevant for flow rate	0.311 ft
Min. bending radius	0.197 ft
Temperature dependent working pressure	-14.4 ... 203 Psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-] Water as per manufacturer's declaration at <a href="http://www.festo.com">www.festo.com</a>
PWIS conformity	VDMA24364-B1/B2-L
Food-safe	See Supplementary material information
Ambient temperature	-22 ... 176 °F
Product weight according to length	0.881 oz/ft
Pneumatic connection	for push-in connector outside diameter 5/8"
Color	neutral
Shore hardness	D 52 +/-3
Materials note	Conforms to RoHS
Material tubing	PE