

Plastic tubing

PLN-3/16-BL-150-CB

Part number: 569914

FESTO

highly resistant to chemicals and hydrolysis.



Data sheet

Feature	Value
Outer diameter, inches	3/16
Bending radius relevant for flow rate	0.095 ft
Min. bending radius	0.036 ft
Temperature dependent working pressure	-14.4 ... 203 Psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com
PWIS conformity	VDMA24364-B1/B2-L
Food-safe	See Supplementary material information
Ambient temperature	-22 ... 176 °F
Product weight according to length	0.107 oz/ft
Pneumatic connection	For push-in connector outside diameter 3/16"
Color	blue
Shore hardness	D 52 +/-3
Materials note	Conforms to RoHS
Material tubing	PE