

# Plastic tubing PUN-V0-14X2-SW-C

Part number: 570351

FESTO

Flame retardant



## Data sheet

Feature	Value
Outside diameter	14 mm
Bending radius relevant for flow rate	70 mm
Inside diameter	9.8 mm
Min. bending radius	45 mm
Tubing characteristics	Suitable for energy chains
Operating pressure for entire temperature range	-0.095 ... 0.6 MPa
Operating pressure complete temperature range	-0.95 ... 6 bar
Operating pressure for entire temperature range	-13.775 ... 87 psi
Temperature-dependent operating pressure	-0.095 ... 0.9 MPa
Temperature dependent working pressure	-0.95 ... 9 bar
Temperature-dependent operating pressure	-13.775 ... 130.5 psi
Note on working pressure	Water: max. 0.6 MPa at max. 50°C
Authorization	TÜV
Certificate issuing department	B 013277 0506 00
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-] Water (liquid, free of ice)
Material fire test	UL94 V-0 (3mm) UL94 V-2 (0,75mm)
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-35 ... 60 °C
Note on ambient temperature	For unpressurised use up to 90 °C
Product weight according to length	0.096 kg/m
Pneumatic connection	For push-in connector outside diameter 14 mm
Color	Black
Note on color	Due to flame protection deviation from the standard color
Shore hardness	D 54 +/-3
Materials note	Conforms to RoHS
Material tubing	TPE-U(PU)