


Linear gantry DHSL-4-EGC80TB-EGC70BS

Part number: 574516

FESTO

Please click above on symbol FAX request, to obtain a non-binding offer to fulfill your requirements.



Data sheet

Feature	Value
Assembly	Linear gantry 4
Effective load	0 ... 4 kg
Drive unit, Z axis	EGC-70-BS
Drive system, Z axis	Electrical With spindle
Intermediate position, Z axis	Any
Stroke, Z axis	0 ... 600 mm
Repetition accuracy in the end position, Z axis	± 0,02 mm
Repetition accuracy in the intermediate position, Z axis	± 0,02 mm
Drive unit, Y axis	EGC-80-TB
Drive system, Y axis	Electrical Toothed belt actuator with ball bearing guide
Intermediate position, Y axis	Any
Stroke, Y axis	0 ... 8,500 mm
Repetition accuracy in the end position, Y axis	± 0,08 mm
Repetition accuracy in the intermediate position, Y axis	± 0,08 mm