


# Linear gantry

## DHSL-15-EGC120TB-EGC80BS

Part number: 574533

FESTO

Please click above on symbol FAX request, to obtain a non-binding offer to fulfill your requirements.



### Data sheet

Feature	Value
Assembly	Linear gantry 15
Effective load	0 ... 15 kg
Drive unit, Z axis	EGC-80-BS
Drive system, Z axis	Electrical With spindle
Intermediate position, Z axis	Any
Stroke, Z axis	0 ... 200 mm
Repetition accuracy in the end position, Z axis	± 0,02 mm
Repetition accuracy in the intermediate position, Z axis	± 0,02 mm
Drive unit, Y axis	EGC-120-TB
Drive system, Y axis	Electrical Toothed belt actuator with ball bearing guide
Intermediate position, Y axis	Any
Stroke, Y axis	0 ... 8,500 mm
Repetition accuracy in the end position, Y axis	± 0,08 mm
Repetition accuracy in the intermediate position, Y axis	± 0,08 mm