


# Push-in/threaded L-fitting, long QBLL-1/8-5/16-U-M

Part number: 576050

FESTO

360° orientable, male thread with external hexagon.



## Data sheet

| Feature   | Value   |
|---|---|
| Size  | Standard  |
| Nominal size                                    | 0.236 "   |
| Type of seal on screw-in stud                   | coating   |
| Design  | L-shape, long   |
| Container size                                  | 10  |
| Operating pressure for entire temperature range | 0.095 ... 1 MPa   |
| Operating pressure complete temperature range   | 0.95 ... 10 bar   |
| Operating pressure for entire temperature range | 13.775 ... 145 psi                                      |
| Maritime classification                         | see certificate   |
| Operating medium                                | Compressed air in accordance with ISO8573-1:2010 [7:::] |
| Note on operating and pilot medium              | Lubricated operation possible                           |
| Corrosion resistance classification CRC         | 1 - Low corrosion stress                                |
| PWIS conformity                                 | VDMA24364 zone III                                      |
| Ambient temperature                             | 0 ... 60 °C   |
| Product weight                                  | 1.259 oz  |
| Mounting type                                   | External hex A/F 14                                     |
| Pneumatic connection, port 1                    | Male thread R1/8  |
| Pneumatic connection, port 2                    | for tubing, 5/16" outside diameter                      |
| Ambient temperature Fahrenheit                  | 32 ... 140 °F   |
| color of release ring                           | Grey  |
| Materials note                                  | Conforms to RoHS  |
| Material housing                                | PBT   |
| Material of threaded seal                       | NBR   |
| Material release ring                           | POM   |
| Material of tube retaining claw                 | High alloy steel, non-corrosive                         |