


Pressure gauge MA-63-0,25

Part number: 7169

FESTO

With display unit in bar and psi.



Data sheet

Feature	Value
Indicating range [bar]	0 ... 0.25 bar
Display range	0 ... 3.6 psi
Conforms to standard	DIN EN 837-3
Nominal size of pressure gauge	63
Mounting type	Line installation
Operating medium	Fluid media Gaseous media
Working pressure	0 ... 0.25 bar
Alternating load factor	0.9
Continuous load factor	0.75
Measurement accuracy class	1,6
Protection class	IP43
Medium temperature	-20 ... 80 °C
Ambient temperature	-20 ... 60 °C
PWIS conformity	VDMA24364-B1/B2-L
Position of connection	Rear side central
Pneumatic connection	G1/4
Material of threaded plug	Brass
Material housing	Steel
Material screen	PMMA
Product weight	180 g
Note on operating and pilot medium	No acetylene No oxygen