

# Multi-plug KSV-8

Part number: 7558

FESTO



## Data sheet

| Feature                                 | Value   |
|---|---|
| Nominal size                            | 4 mm  |
| Working pressure                        | -0.95 ... 16 bar  |
| Operating medium                        | Compressed air in accordance with ISO8573-1:2010 [7:-:-]                    |
| Note on operating and pilot medium      | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress   |
| PWIS conformity                         | VDMA24364-B1/B2-L   |
| Medium temperature                      | -10 ... 60 °C   |
| Ambient temperature                     | -10 ... 60 °C   |
| Product weight                          | 128 g   |
| Max. number of connections              | 8   |
| Pneumatic connection                    | PK-2<br>PK-3<br>PK-4  |
| Color                                   | Grey  |
| Materials note                          | Conforms to RoHS  |