

Common supply manifold VABM-B10-25-G12-3-P53

Part number: 8026220

FESTO



Data sheet

| Feature | Value |
|---|-------------------------------|
| Grid dimension | 27.5 mm |
| Assembly position | Any |
| Max. number of valve positions | 3 |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Product weight | 340 g |
| Mounting type | With mounting bracket |
| Pneumatic connection, port 1 | G1/2 |
| Materials note | Conforms to RoHS |
| Material manifold | Wrought Aluminum alloy |