


Common supply manifold OABM-P-G3-15-8

Part number: 8049146

FESTO



Data sheet

Feature	Value
No. of device positions	8
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Max. tightening torque	3.3 Nm
Min. tightening torque	0.3 Nm
Product weight	172 g
Mounting type	with through hole
Pneumatic connection, port 1	G1/8
Materials note	Conforms to RoHS
Material of connecting plate	Wrought Aluminum alloy