


Parallel kit EAMM-U-60-D40-58AA-91

Part number: 8058940

FESTO

Suitable for electric drives.



Data sheet

Feature	Value
Size	60
Assembly position	Any
Max. speed	6,000 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Mass moment of inertia	26.7 kgmm ²
No-load driving torque	0.07 Nm
Transferable torque	3 Nm
Product weight	1,150 g
Interface code, actuator	D40
Interface code, motor in	58AA
Materials note	Conforms to RoHS