


# Electronics module VMPA14-FB-EMG-8

Part number: 8066765

FESTO



## Data sheet

Feature	Value
Diagnosis	Undervoltage, valves
Max. number of valve positions	4
Max. number of solenoid coils	8
Intrinsic current consumption at load voltage	23 mA
Intrinsic current consumption at operating voltage	8 mA
Nominal breakaway current per solenoid coil	58 mA up to 24 ms
Nominal current with current reduction	9 mA after 24 ms
Corrosion resistance classification CRC	1 - Low corrosion stress (when installed)
PWIS conformity	VDMA24364-B1/B2-L
Product weight	30 g
Material housing	POM
Materials note	Conforms to RoHS