


Service unit MS6-EM1FR-1/2-D6-E-P-M-AG-BAR-WPE-B

Part number: 8098365

★ Core product range

FESTO



Data sheet

| Feature | Value |
|---|--|
| Size | 6 |
| Series | MS |
| Assembly position | Vertical +/- 5° |
| Pressure gauge | with pressure gauge |
| Operating pressure MPa | 0.1 ... 1 MPa |
| Working pressure | 1 ... 10 bar |
| Standard flow rate exhaust 0.6->0 MPa (6->0 bar, 87->0 psi) | 3,600 l/min |
| Standard nominal flow rate | 5,300 l/min |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Compatibility with ester oil not guaranteed |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Storage temperature | -5 ... 50 °C |
| Medium temperature | -5 ... 50 °C |
| Ambient temperature | -5 ... 50 °C |
| Product weight | 1,250 g |
| Mounting type | Line installation With mounting bracket with accessories Optional |
| Materials note | Conforms to RoHS |