


# Axial kit EAMM-A-D50-80PB

Part number: 8123493

FESTO



## Data sheet

Feature	Value
Assembly position	Any
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	17 Nm
Product weight	892 g
Interface code, actuator	D50
Interface code, motor in	80PB 80R
Materials note	Conforms to RoHS