

Spirala snopa savitljivih cijevi PKB-50-BL

Broj artikla: 3656

FESTO



Tehnički podaci

Svojstvo	Vrijednost
Veličina	For tube bundle diameter max. 50 mm
Vanjski promjer	6 mm
Unutarnji promjer	4 mm
Upute za korištenje	12 tubes with an outside diameter of 12 mm 28 tubes with an outside diameter of 8 mm 50 tubes with an outside diameter of 6 mm 60 tubes with an outside diameter of 4 mm
Tube length	50 m
PWIS conformity	VDMA24364-B2-L
Težina proizvoda prema duljini	0,0146 kg/m
Boja	plavo
Materijal - napomena	RoHS sukladno
Material tubing	PE