

# Zaporni vijak NPQH-BK-M5-P10

Broj artikla: 578404

FESTO



## Tehnički podaci

Svojstvo	Vrijednost
Veličina	Standard
Način brtvljenja na navojnom čepu	Brtveni prsten
Položaj ugradnje	proizvoljno
Oblik	Plug screw
Veličina pakiranja	10
Operating pressure for entire temperature range	-0,095 ... 2 MPa
Pogonski tlak kompletnog temperaturnog područja	-0,95 ... 20 bar
Operating pressure for entire temperature range	-13,775 ... 290 psi
Uputa za pogonski tlak	Water: max. 0.6 MPa at 0 - 50 °C
Mjesto izdavanja certifikata	NSF C0523185
Pogonski medij	Komprimirani zrak prema ISO 8573-1:2010 [7:-:-] Water (liquid, free of ice)
Uputa o mediju pogona i upravljanja	Moguć nauljeni pogon
Klasa korozione otpornosti KBK	3 - visoka otpornost na koroziju
PWIS conformity	VDMA24364-B1/B2-L
Klasa čistog prostora	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Sigurnost hrane	Pogledajte izjavu o sukladnosti NSF/ANSI 169
Temperatura okoline	0 ... 150 °C
Nazivni moment pritezanja	1 Nm
Tolerancija uz nazivni moment pritezanja	± 20 %
Težina proizvoda	0,8 g
Vrsta pričvršćenja	Internal hex A/F 2.5
Pneumatski priključak 1	Vanjski navoj M5
Materijal - napomena	RoHS sukladno
Material housing	Brass, chemically nickel-plated
Material of threaded seal	FPM