

# Conector cu afisaj MFL-24DC/AC

Cod: 10004

FESTO

cu diode luminoase (LED)



## Fisa tehnica

Caracteristica	valoare
Greutate produs	15 g
Conectare electrica	Oglinda de conectare tip B conform EN 175301-803 conform standard industrial (11 mm)
Tensiune nominala de operare DC	24 V
Tensiune nominala de operare AC	24 V
Frecventa de retea	0 ... 60 Hz
Oscilatii admisibile ale tensiunii	+/- 15 %
Tip de protectie	IP65 conform IEC 60529
Temperatura mediului	-20 ... 60 °C
Conformitatea PWIS	VDMA24364-B2-L
Materialul carcasei	PA6 ranforsat