

Set de montaj CRSMBR-40

Cod: 163889

FESTO

Rezistent la coroziune, pentru cilindri pneumatici tip CRDSNU,
CRDSW si CRDG



Fisa tehnica

Caracteristica	valoare
marime de fabricatie	40
Conformitatea PWIS	VDMA24364-B2-L
Cuplu de pornire	0,5 Nm