


Modul sursa de alimentare CDVI5.0-EB2X-MP-MO

Cod: 548436

FESTO



Fisa tehnica

Caracteristica	valoare
lungime	56 mm
numarul max. de pozitii de ventile	2
clasa de rezistenta la coroziune KBK	3
greutate produs	510 g
tip fixare	cu filet interior si bolt
racord pneumatic 1	G1/8
racord pneumatic 2	G1/8
racord pneumatic 3	G1/8
racord pneumatic 4	G1/8
racord pneumatic 5	G1/8
indicatie material	conform RoHS