

Tija
VMPAL-ZAS-45
Cod: 561117

FESTO



Fisa tehnica

Caracteristica	valoare
Lungime	45 mm
Marimea legaturii	3
Clasa de rezistenta la coroziune KBK	3 - Rezistenta ridicata la coroziune
Conformitatea PWIS	VDMA24364-B1/B2-L
Temperatura mediului	-5 ... 50 °C
Cuplu de strangere maxim	1,7 Nm
Greutate produs	33 g
Indicatie material	conform RoHS
Materialul tirantilor	otel inoxidabil aliaj inalt