

Tija
VMPAL-ZAS-165
Cod: 561120

FESTO



Fisa tehnica

| Caracteristica | valoare |
|--------------------------------------|--------------------------------------|
| Lungime | 165 mm |
| Marimea legaturii | 3 |
| Clasa de rezistenta la coroziune KBK | 3 - Rezistenta ridicata la coroziune |
| Conformitatea PWIS | VDMA24364-B1/B2-L |
| Temperatura mediului | -5 ... 50 °C |
| Cuplu de strangere maxim | 1,7 Nm |
| Greutate produs | 114 g |
| Indicatie material | conform RoHS |
| Materialul tirantilor | otel inoxidabil aliaj inalt |